



TECHNOLOGY IN MOTION

MACO RAIL-SYSTEMS

SLIDING HARDWARE



ASSEMBLY INSTRUCTIONS

HS COMFORT CLOSE / COMFORT STOP
concealed with reinforcement 1130522
Veka Slide 70/82

Table of contents

Important instructions	3
Function	3
Fittings overview	4 - 5
Preparation frame - Example: scheme A and C	6
Preparation sash	7
Mounting Comfort Close/Comfort Stop	8
Mounting sash and frame	9
Reference dimension	9
Completion of guide track	10
Adjustment options	10
Mounting cover frame piece	11
Technical data	11

Important instructions


Target group

This documentation is intended exclusively for specialist companies and certified specialists. The work described herein must only be carried out by certified specialists.

Usage and safety information

In addition to this information, the profile-dependent assembly instructions for HS-Hardware Veka Slide, Order No. 759119, must be complied with. In the Comfort Close assembly instructions, only the differences from the above document are described. Mount all hardware parts professionally as described in this manual and observe all safety instructions.


Function



Fittings overview

Pos.	Description
6.1	Guide Track
15.1	Comfort Close
15.2	Comfort Stop
16.1	Packer housing
16.2	Frame piece
16.3	Cover frame piece
16.4	Packer frame piece
16.5	Packer frame piece (3mm)
16.7	Screw-on bracket Comfort Close/Safety Stop
16.8	Bracket Comfort Close/Safety Stop

Note: All measurements in this document are indicated in millimetres.






Fittings overview

Items per sliding sash

	Article description			Item Code
1	Comfort Close 15.1 ^{z)}	size 1	≤ 200 kg ≤ 30 N sash weight Sliding force	300359
		size 2	> 200 ... 300 kg ≤ 50 N sash weight Sliding force	300360
1 ^{x)}	Comfort Stop 15.2 ^{z)}	size 1	≤ 200 kg ≤ 30 N sash weight Sliding force	304052
		size 2	> 200 ... 300 kg ≤ 50 N sash weight Sliding force	304053
	Accessories Comfort Close + Comfort Stop 16.1, 16.4, 16.5, 16.7, 16.8			305152
1	Accessories Comfort Close + Comfort Stop 16.1, 16.4, 16.5, 16.7, 16.8			305152
1	Frame piece, adjustable 16.2			305134
1	Cover frame piece 16.3			304816

^{x)} optional

^{z)} Colour of damper: size 1 - black, size 2 - silver-grey





Preparation sash

- › Mounting of the Comfort Close at non-handle side or Comfort Stop at handle side.



The reinforcement „1130522“ has to be within the area of Comfort Close respectively Comfort Stop (slide in max. 110 mm to outer edge of sash).

- › (2) The fitting groove must be free of burrs.
- › (3) Position bracket (16.8) with packer (16.1) at the sash. Pre-drill the holes with $\varnothing 4.2$. Fasten bracket and packer with screws 4.8 x 25.
- › (4) Drill holes for screw-on bracket (16.7) with $\varnothing 4.2$.
- › (5) Hanging the sash.




The sash has to slide smooth-running.

Mounting Comfort Close/Comfort Stop

- › (1) Comfort Close respectively Comfort Stop has to be pretensioned.
- › (2) Clip packer onto the housing of the Comfort Close and/or onto the housing of the Comfort Stop.
- › Insert the housing into the half opened sash from middle post until bracket (16.8)
- › (3) Mount screw-on bracket (16.7) with 3 screws 4.8 x 16.



The Comfort Close or Comfort Stop has to be fixed at both ends within reinforcement. Other wise the Comfort Close or Comfort Stop can be damaged while opening/ closing the sash. Risk of injury!




Mounting sash and frame



Attention: Risk of injury due to fallen sash!


To avoid the risk of injury, perform the following steps with two workers.

- › (1) Set down the sliding sash onto the running track in the area of the fixed sash and swivel it into the element.
- › (2) Bring handle into „Open“ position and slide the sliding sash to the transit area.



Reference dimension

- › To check the height of the frame piece, swivel in the sash, lift it and slide into closing position.
- › Measure reference dimension within the range of the comfort close respectively comfort stop (desired value = 6.5 mm).
- › If necessary, slide the sash aside and compensate deviation to the reference dimension by adjustment of the frame piece (refer to „Adjustment options“).
- › Fasten guide track on fixed sash side.




Completion of guide track

(If the guide track is not divided,
this work step is not necessary.)

Example:

scheme A; scheme C accordingly

Fasten the guide track at frame profile.




Adjustment options

In case of inaccuracy concerning position of the frame piece, the reference dimension concerning the height of the frame piece and the end position of the sash related to the frame can be adjusted.

To do this, the sash has to be opened.


- › (1) Correction of the lateral position (+/- 5 mm):
 - (1.1) Loosen screw by means of Torx 25,
 - (1.2) Slide frame piece into the desired direction:
 - 0 – 5 mm: closing of sash will be shifted in direction of handle side;
 - 0 + 5 mm: closing of sash will be shifted in direction of non-handle side
- › (1.3) Fasten screw with max. 3 Nm.
- › (2) Correction of the height of the frame piece (+ 3 mm) with Torx 15.

Adjustment at
closing edge




(Sash opened))

0 – 5 mm: towards closing position (frame)
0 + 5 mm: off the closing position (frame)



**Note: Adjustments may be changed after glazing
the sash and mounting the frame!**

Mounting cover frame piece



Technical data

Range of application scheme A:

Sash width (FB)	730 – 3320 mm
FB _{min.} for 2x Comfort Close	1000 mm
Sash height (FH)	770 – 2880 mm
Outer frame width (RAB)	acc. to profile manufacturer's specifications
Sash weight or sliding force without Comfort Close and Comfort Stop	size 1: max. 200 kg or max. 30 N size 2: max. 300 kg or max. 50 N (further sizes on request)

Depending on version of the profile sealing to be used, it can happen, that the sash cannot close completely.

Dimensions (W x H x D)	
Comfort Close	336 mm x 27.5 mm x 22 mm
Comfort Stop	336 mm x 27.5 mm x 22 mm
Soft move-in	starting approx. 100 mm off the closing edge
Increase of sliding force with Comfort Close or Comfort Stop	size 1: by 25 N (black) size 2: by 45 N (silver-grey)

Range of application is depending on used profile systems. Specifications of profile manufacturers to be observed.

You want everything from a single source?

We provide you with complete solutions for sliding doors, windows and doors – for timber, PVC and aluminium. Experience our versatile system offer, comprehensive service included. Discover more of this on our website **www.maco.eu** or contact your MACO representative.



MACO near you:
www.maco.eu/contact



TECHNOLOGY IN MOTION



This print document is revised regularly.
The latest version is available at <http://www.maco.eu/assets/757736>
or by scanning the QR code.

Created: 01/2019 - Changed: 26.08.2020
Order no. 757736
All rights reserved and subject to change.